DLRO 200

Digital Microhmmeter



- Small and weighs less than 15 kg (33 lbs)
- Test currents from 10 A to 200 A d.c.
- 0.1 $\mu\Omega$ best resolution
- On board memory for up to 300 test results and notes
- RS232 port to download stored results or for real time output to a printer
- Supplied complete with 5m (16.4 ft.) test leads and download software
- Smooth, continuous applied current eliminates magnetic transients capable of inductively tripping breaker controls (115 V version)

DESCRIPTION

Megger DLRO200 measures resistances between 0.1 $\mu\Omega$ and 1 $\Omega,$ at high currents.

This versatile instrument can provide test currents from 10 amps up to 200 amps subject to the load resistance and supply voltage. A large liquid crystal display provides all the information needed to perform a test; all test parameters and measurement results are displayed.

The unique design allows the weight and size of DLRO200 to be kept to a minimum; the instrument weighs less than 15 kg. This small size makes DLRO200 equally at home in the workshop,on the production floor or in the field. The high current capability and compact design make DLRO200 suitable for testing circuit breaker contacts, switch contacts, busbar joints or other applications where high current is needed.

300 sets of results may be stored in DLRO200's on board memory for later download to a PC or may be output directly to a printer via the RS232 port. You may also add notes to any stored result by using the on board alphanumeric keypad, thereby making later identification of results straightforward.

As well as adding notes to stored results, the alphanumeric keypad allows you to set the test current directly by typing in the value required. DLRO200 will check the continuity of the test circuit, and will quickly ramp the test current up to the desired level. The keyboard is also used to set upper and lower limits for the result and to prevent the use of excessive currents by setting an upper limit to the allowable test current.

DLRO200 uses a four terminal measurement technique to cancel the resistance of the test leads from the measurement.

History of 'Ducter' testing

For over 100 years the 'Ducter test' has been used to describe a simple test for measuring very low contact resistances and "Ducter", which is still used as a trade mark, was the name originally given to the low resistance ohmmeter manufactured by Megger. The name Ducter was registered by Megger in June 1908 and 'Ducter' has since become the industry standard.

Test Modes

DLRO200 operates in one of three modes, which are simply selected from the on screen menu.

CONTINUOUS mode is provided for users who wish to monitor a resistance over a period of time. Connect the test leads, select the test current and press the TEST button. DLRO200 will pass a current continuously, and measure the resulting voltage at 2- second intervals, until the test button is pressed to stop the test or the test circuit is interrupted.

In NORMAL mode you connect the leads, select the test current and press the TEST button. The test current will ramp up to the desired level, hold for 2 seconds and then ramp down. The whole process takes approximately 10 seconds.

In AUTO mode select the desired current, connect the current leads and press the TEST button. The TEST lamp will flash to show that the DLRO200 is ready to carry out a test. As soon as the potential leads are connected, a test will start. To repeat a test, simply break contact with the voltage probes and remake contac.

Measuring individual joints in a busbar is a good example of the convenience to be gained by using AUTO mode. The two current leads are connected to the ends of the busbar. They will remain connected here until all tests have been completed. When the voltage leads make contact across a joint, DLRO200 detects that all four leads

DLRO 200

Digital Microhmmeter



are connected, carries out a test and stops. When you move to the next joint DLRO detects the new completed circuit automatically and carries out the next test, and so on until all joints have been tested. The results may be stored automatically and may be recalled to the display or downloaded for review.

SPECIFICATIONS

Measurement:

Range: 0.1 $\mu\Omega$ to 999.9 $m\Omega$

(Subject to supply voltage and leads used)

Accuracy: Voltage $\pm 0.5\% \pm 0.1 \text{ mV}$

Current ±0.5% ± 0.1 A Resistance: Better than 1% from 300 $\mu\Omega$ to 100 m Ω

Better than ±2% from 100 $\mu\Omega$ to 300 $\mu\Omega$

Current Lead Resistance (Megger supplied leads)

2 x 5 m 25 mm2 current leads 8 m 2 x 5 m 50 mm2 current leads 4 m Ω 2 x 10 m 70 mm2 current leads 5.4 m Ω 2 x 15 m 95 mm2 current leads 6 m Ω

Maximum Continuous Test Time

More than 10 minutes at 200 A @

20 °C ambient.

Power Supply for DLRO200 for full output (unsmoothed d.c.)

100 to 265 V 50/60 Hz with a load less than 19 $m\Omega$ (supply >207 V rms), or

11 $m\Omega$ (115 V rms) including

current leads

Power Supply for DLRO200-115 V for full output (additional smoothing)

100 to 130 V 50/60 Hz with a load less

than 11 $\mbox{m}\Omega$ including current leads

Test Modes: Manual, Auto, Continuous.

Test Time: 10 seconds NORMAL /AUTO mode.

Refreshed every 2 seconds in

CONTINUOUS mode

Display: Large, high resolution backlit liquid

crystal display

Warnings Current flowing: - LED. Other warnings

are shown on the lcd display

Real time or batch download via RS232 using Download Manager.

Storage Capacity: 300 result sets and memo,

battery backed for 10 years.

Memo field: 160 characters max.

Test Current

Data Transfer

Range: 10 A to 200 A d.c. *

Accuracy: $\pm 2\% \pm 2 \text{ A}$

Voltmeter input impedance: >200 kΩ

Hum rejection: 5 V rms 50 Hz/60 Hz

Temperature Operation: -10 to +50 °C (-14 to +122 °F)

Storage: -25 to +65 °C (-13 to 149 °F)

Calibration: 20 °C

Co-efficient: <0.05% per °C

Max. Humidity: 95% RH non-condensing

 Maxi Altitude:
 2000 m

 Safety:
 IEC61010-1

 EMC:
 IEC61326-1

Dimensions: 410 x 250 x 270 mm

(16.4 x 9.84 x 10.63 ins)

Weight: 14.5 kg (excluding test leads)

(31.97 lbs)

ORDERING INFORMATION			
STANDARD VERSIONS WITH TEST LEADS		VERSIONS WITHOUT TEST LEADS	
Description	Part number	Description	Part number
DLRO200 High Current Digital Low Resistanc Ohmmeter (English QWERTY keyboard)	e DLRO200-EN	DLRO200 High Current Digital Low Resis Ohmmeter (English QWERTY keyboard)	tance DLRO200-EN-NLS
DLRO200 High Current Digital Low Resistanc Ohmmeter (French AZERTY keyboard)	e DLRO200-FR	DLRO200 High Current Digital Low Resis Ohmmeter (French AZERTY keyboard)	tance DLRO200-FR-NLS
DLRO200-115 High Current Digital Low Resistance Ohmmeter 115 V with additional output smoothing (English QWERTY keyboard) DLRO200-115		DLRO200-115 High Current Digital Low Resistance Ohmmeter 115 V with additional output smoothing (English QWERTY keyboard) DLRO200-115-NLS	
Included accessories		Included accessories	
DLRO200-EN, DLRO200-FR		Download Manager	6111-442
5 m (16.4 ft.) Lead set set comprising 2 x 50 mm2 current leads with clips and 2 potential		User Guide on CD-ROM	6172-763
		RS232 download cable	25955-025
leads with clips	6220-755	Quick Start Guide (English)	6172-782
DLRO200-115		Quick Start Guide (French)	6172-783
5 m (16.4 ft.) Lead set in bag comprising:		Warranty card.	6170-618
2 x 25 mm2 current leads with clamps and 2 x potential leads with clips	6220-787		
Download Manager	6111-442	NOTE:	
User Guide on CD-ROM	6172-763	For further test lead information refer to datasheet DLRO_TL_DS_	
RS232 download cable	25955-025	en_V01.pdf	
Quick Start Guide (English)	6172-782	-	
Quick Start Guide (French)	6172-783	-	
Warranty card.	6170-618	-	

TEST LEAD INFORMATION



6220-755 5m Lead set (600 A) 2 x 50 mm 2 current leads with clamps and 2 x potential leads with clips. 6220-787 5m Lead set (200 A) as above but 25 mm 2 cable fitted.

DESCRIPTION

Lead set consists of pair of flexible high current capacity leads, together with a separate pair of lightweight potential leads.

Current leads are fitted with heavy duty sprung clamps (60 mm jaw capacity). Potential leads fitted with smaller HD crocodile clips 22 mm jaw capacity).

Note:

6220-755 supplied as standard with DLRO200-EN and DLRO200-FR

6220-787 supplied as standard with DLRO200-115



6220-756 10m Lead set2 x 70 mm2 current leads with clamps and 2 x potential leads with clips.

6220-757 15m Lead set2 x 95 mm2 current leads with clamps and 2 x potential leads with clips.

DESCRIPTION

Lead set consists of pair of flexible high current capacity (600 A cont.) leads, together with a separate pair of lightweight potential leads.

Current leads are fitted with heavy duty sprung clamps (60 mm jaw capacity). Potential leads fitted with smaller HD crocodile clips 22 mm jaw capacity).

SALES OFFICE

Megger Limited Archcliffe Road Dover CT17 9EN England T +44 (0) 1304 502101 E UKsales@megger.com

DLRO200_DS_en_V06

www.megger.com ISO 9001 The word 'Megger' is a registered trademark

